

**Garant**
**Fluteless machine tap without oil grooves HSS-E-PM 6HX, TiN, M: M8**

**Order data**

Order number	139125 M8
GTIN	4045197508720
Item class	11H

**Description**
**Version:**

 Size M1–M1.4 – **tolerance class:** ISO 1X / 4HX

**DIN 2174** ( $\approx$  **DIN 371**  $\leq$  M10;  $\approx$  **DIN 376**  $\geq$  M12).

 The **innovative polygon form** permits a wide application spectrum. The **multi-function layer structure** achieves **maximum service life** even in **high-tensile materials**.

Tolerance class: ISO 2X 6HX

Thread pitch: 1.25 mm

Overall length L: 90 mm

 Shank  $\varnothing D_s$ : 8 mm

 Shank square  $\square$ : 6.2 mm

 Tapping hole  $\varnothing$  guide value: 7.45 mm

**Technical description**

Number of cutting edges Z	5
Number of clamping slots	5
Thread $\varnothing$	8 mm
Thread pitch	1.25 mm
Shank $\varnothing D_s$	8 mm
Shank square $\square$	6.2 mm
Overall length L	90 mm
Tapping hole $\varnothing$ guide value	7.45 mm
Tolerance class	ISO 2X 6HX

Thread depth	12 mm
Thread size	M8
Coating	TiN
Thread type	M
Flank angle	60°
Tool material	HSS E PM
Standard	DIN 2174
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 1.5×D for through holes
Application for type of drilling	up to 1.5×D for blind holes
Cutting direction	right-hand
Colour ring	green
Type of product	Fluteless tap

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu plastics	suitable only under restricted conditions	42 m/min	N
Aluminium (short chipping)	suitable	42 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	37 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	32 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	27 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	22 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable only under restricted conditions	17 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	12 m/min	M

CuZn	suitable only under restricted conditions	22 m/min	N
Uni	suitable		
Oil	suitable		
wet maximum	suitable		