



## Pneumatic orbital sander, Type: 69029

### Order data

Order number	079656 69029
GTIN	616026690295
Item class	03R

### Description

#### Version:

Powerful orbital sander with urethane hook and loop backing pad  $\varnothing$  150 mm. **Easy to use** due to light-weight composite housing and ergonomic hand application area. **Robust, smooth-running**, and **low-vibration pneumatic drive** with steel cylinder, low noise level. For **roughing and intermediate** sanding with 5 mm orbital stroke. Connection for **external extraction** including hook and loop pad No. 079690 size 22290.

#### Supplied with:

Including the necessary coupling adaptors.

#### Note:

See No. 567775 for velour abrasive discs.

DynaMaze hook and loop pads for No. 079655 and 079656 can be found under No. 079690 size 22290.

maximum speed: 12000 rpm

maximum air consumption: 450 l/min

Type of extraction: External

Orbital stroke: 5 mm

Weight: 0.8 kg

Operating noise: 77 dB(A)

### Technical description

Warranty period for the machine	a
Type of product	