

bimos

Neon swivel work chair, synthetic leather, with castors, low, Colour: BLUE**Order data**

Order number	965438 BLUE
GTIN	4016849549835
Item class	96J

Description**Version:**

Neon swivel work chair with interchangeable cushion system. The cushion elements are simply mounted and fixed with a click. With ergonomic adjustment options: Synchronous technology with weight adjustment, seat height adjustment using gas pressure safety spring, seat angle adjustment, seat depth adjustment, backrest height adjustment. With flexible band running all around the edge in different colours.

Seat and backrest with synthetic leather cladding, comfortable and soft. Washable and easy-care, resistant to oils and disinfectants.

Standard:**DIN 68877****Optional extras:**

Pair of multi-function armrests No. 965455.

Technical description

Support frame version	5-point star base
Height adjustment version	Gas pressure spring

Material of base	Aluminium matt powder coated
Lumbar support	yes
Roller version	Load-responsive castor braking for hard floors.
Synchro mechanism	yes
Colour of seat material	black
Seat width	470 mm
Continuous contact backrest adjustment	no
Material of seat surface	Synthetic leather
Series	Neon
Standard	DIN 68877
Type of height adjustment	Height adjustment lever
Armrest pair can be adjusted	yes
Base version	Set of castors
Backrest height	570 mm
Seat depth adjustment range	420 - 480 mm
Colour of the strap	blue
Load capacity chair	120 kg
Height adjustment range	450 mm
Type of product	Swivel work chair