



Machine tap HSS-E-PM Form B 6HX, TiCN, M: M10



Order data

Order number	132170 M10
GTIN	4045197265449
Item class	11H

Description

Version:

Strong spiral point.

Guide section with oil grooves, but without chip flutes. For use with **emulsion** (fat content minimum 8%).

Note:

NEW GENERATION AVAILABLE!

Recommended successor product is No. 132180.

Thread type: M

Tool material: HSS E PM

Norm: DIN 371

Tolerance class: ISO 2X 6HX

Thread pitch: 1.5 mm

Overall length L_{tot} : 100 mm

Shank \varnothing : 10 mm

Shank square: 8 mm

Tapping hole \varnothing : 8.5 mm

Technical description

Thread pitch	1.5 mm
Number of clamping slots	3
Tapping hole \varnothing	8.5 mm
Number of cutting edges Z	3
Taper lead angle	50 degrees
Thread \varnothing	10 mm

Norm	DIN 371
Shank Ø	10 mm
Overall length L _{tot}	100 mm
Shank square	8 mm
Tolerance class	ISO 2X 6HX
Tool material	HSS E PM
Thread depth	20 mm
Thread type	M
Thread size	M10
Coating	TiCN
Flank angle	60 degrees
Thread standard	DIN 13
Taper lead form	B
Skaft	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	blue