

Garant**Machine tap HSS-E-PM, nitrided + vaporised, M: M4****Order data**

Order number	132420 M4
GTIN	4045197071538
Item class	11H

Description**Version:**

Strong spiral point. Guide section with oil grooves, but without chip flutes.

Advantage:

Particularly strong, optimum self-guidance and no recutting when reversed.

Thread type: M

Tool material: HSS E PM

Standard: DIN 371

Tolerance class: ISO 2X 6HX

Thread pitch: 0.7 mm

Overall length L: 63 mm

Shank $\varnothing D_s$: 4.5 mm

Shank square \square : 3.4 mm

Tapping hole \varnothing : 3.3 mm

Technical description

Number of cutting edges Z	3
Tapping hole \varnothing	3.3 mm
Number of clamping slots	3
Thread \varnothing	4 mm
Thread pitch	0.7 mm
Standard	DIN 371
Shank $\varnothing D_s$	4.5 mm
Overall length L	63 mm

Shank square <input type="checkbox"/>	3.4 mm
Tolerance class	ISO 2X 6HX
Tool material	HSS E PM
Thread depth	8 mm
Thread type	M
Thread size	M4
Coating	nitrided + vaporised
Flank angle	60°
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	pink
Type of product	Tap

User data

	Suitability	V _c	ISO code
Hybrids	suitable		
Ti > 850 N/mm ²	suitable	6 m/min	S
Inconel	suitable	2 m/min	S
MMC	suitable only under restricted conditions		
Oil	suitable		
wet maximum	suitable		