



## Parting-off tool, neutral, Blade height $h_5$ : 26mm



### Order data

Order number	278005 26
GTIN	4062406380762
Item class	22B

### Description

#### Version:

All sizes with just one insert seat for two groove widths (3 mm and 4 mm). For grooving inserts No. 278029 – 278036.

#### Suitable for:

Parting-off tool for parting-off inserts No. 278029 – 278036.

#### Attention:

Parting-off insert can be clamped only in combination with base holders No. 278008 and 278009. The parting-off insert is easily replaced only by releasing the front screw on the clamping strip of the base holder.

#### Note:

From 14 mm groove depth onwards the second cutter comes into contact with the workpiece. This can lead to scoring.

### Technical description

Blade height $h_5$	26 mm
Width $b_2$	2.6 mm
Groove width $w$	3; 4 mm
Height $h_1$	21.4 mm
for maximum workpiece $\varnothing$	60 mm
Overall length $L$	110 mm
Application type	neutral

Through-coolant	no
axial grooving possible	no
Type of product	Parting-off tool