

**Drill chuck with keyless locking Metal version, Type: 13-1/2****Order data**

Order number	342208 13-1/2
GTIN	4062406381691
Item class	32W

Description**Version:**

- **Keyless drill chuck with self-tightening locking mechanism. No additional locking required (not even for impact drilling).**
- **Very ergonomic, user-friendly, hexagon flats for wrench assistance.**
- **Good concentricity.**
- **Through hole version for right-hand and left-hand operation (thread M5 or M6).**

Special clamping chamfer for wear reduction.

Clamping range: 1.5 - 13 mm

External Ø: 42 mm

Drill head length open: 64.5 mm

Drill head length closed: 71.2 mm

Adapter: 1/2-20 in

maximum machine power: 1100 W

Technical description

Drill head length closed	71.2 mm
External Ø	42 mm
Adapter	1/2-20 in
maximum machine power	1100 W

Clamping range	1.5 - 13 mm
Drill head length open	64.5 mm
Type	13-1/2
Keyless locking mechanism	yes
Type of product	Drill chuck keyless