



Pneumatic chisel hammer, Type: P2551



Order data

Order number	079730 P2551
GTIN	7322590037031
Item class	03R

Description

Version:

Handy **chisel hammer** for chiselling and separating. With good vibration-damping characteristics.

Supplied with:

Including the necessary coupling adaptors.

Spare part:

Selected service kits: Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

Technical description

Tool arbor size	12.7 mm
Tool arbor shape	Square
Operating noise	85 dB(A)
recommended hose size (internal Ø)	10 mm
maximum vibration to EN	6.7 m/s ²
Manufacturer's designation	P2551
Impact frequency	40 Hz
Length	435 mm
maximum air consumption	480 l/min
Weight	2.95 kg

Compressed air connection	1/4 in
Connection thread	BSP
Type of product	Chisel mallet

Accessories

Chisel Dimensions 19X178 mm	079739 19X178
Chisel Dimensions 35X178 mm	079739 35X178