

Garant

GARANT Master Alu SlotMachine solid carbide roughing end mill TPC, DLC, Ø e8 DC: 6mm



Order data

Order number	205274 6
GTIN	4062406381257
Item class	11X

Description

Version:

For roughing.

Special profile for machining non-ferrous metals. Significant reduction in the chip volume due to targeted chip fragmentation using the **special cutter geometry**.

Problem-solver for TPC machining. Ideal for automated production as the risk of chip accumulations in the machine is largely prevented.

Note:

For **HB shanks** use order **no. 205276**.

HB shanks are available at the same price as HA.

h_{max} : The values stated in the table are maximum values.

ae_{max} is $0.15 \times D$ for TPC machining.

Technical description

Average chip thickness h_{max} for TPC milling in short-chipping aluminium	0.043 mm
Overhang length L_1 incl. recess	30 mm
Cutting edge $\varnothing D_c$	6 mm
Direction of infeed	horizontal, oblique and vertical
Overall length L	70 mm
Helix angle	35 degrees
Balance quality with shank	G 2.5 with HA

Shank $\varnothing D_s$	6 mm
Corner rounding r_v	0.2 mm
Recess $\varnothing D_1$	5.7 mm
No. of teeth Z	3
Shank	DIN 6535 HA to h6
Flute length L_c	25 mm
Tolerance nominal \varnothing	e8
Series	Master Alu
Coating	DLC
Tool material	Solid carbide
Standard	Manufacturer's standard
Milling profile	WR
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	0.15×D
Through-coolant	no
Machining strategy	HPC
Colour ring	yellow
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Aluminium	Suitable	400 m/min	N
Aluminium (short chipping)	Suitable	360 m/min	N
Alu > 10% Si	suitable	340 m/min	N
PA 66	suitable only under restricted conditions	110 m/min	N
PEEK	suitable only under restricted conditions	90 m/min	N

Cu	Suitable	140 m/min	N
CuZn	Suitable	180 m/min	N
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable only under restricted conditions		
Air	Suitable		