

Garant

GARANT Master Form Steel fluteless machine tap with oil grooves HSS-E-PM, TiAlN, MF: 12X1,5



Order data

Order number	139280 12X1,5
GTIN	4062406383886
Item class	11I

Description

Version:

GARANT Master Form Steel:

The latest generation of **high-performance fluteless taps** are specially developed for **use in steels**.

- **Optimised polygon geometry for a reduced torque.**
- **Multi-layer HIPIMS coating for high wear resistance.**
- **HSS-E-PM substrate for top process reliability.**

DIN 2174 (\approx DIN 371 \leq M10; DIN 376 \geq M12).

Tolerance class: ISO 2X 6HX

Thread pitch: 1.5 mm

Overall length L: 100 mm

Shank $\varnothing D_s$: 9 mm

Shank square \square : 7 mm

Tapping hole \varnothing guide value: 11.35 mm

Technical description

Shank square \square	7 mm
Number of clamping slots	8
Tapping hole \varnothing guide value	11.35 mm
Shank $\varnothing D_s$	9 mm
Series	GARANT Master

Overall length L	100 mm
Tolerance class	ISO 2X 6HX
Thread depth	36 mm
Thread Ø	12 mm
Number of cutting edges Z	8
Thread size	M12×1.5
Thread pitch	1.5 mm
Coating	TiAlN
Thread type	MF
Flank angle	60°
Tool material	HSS E PM
Standard	DIN 2174
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for blind holes
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Colour ring	without
Type of product	Fluteless tap

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	38 m/min	N
Steel < 500 N/mm ²	suitable	37 m/min	P
Steel < 750 N/mm ²	suitable	35 m/min	P
Steel < 900 N/mm ²	suitable	27 m/min	P

Steel < 1100 N/mm ²	suitable	18 m/min	P
Steel < 1400 N/mm ²	suitable	12 m/min	P
INOX < 900 N/mm ²	suitable	12 m/min	M
INOX > 900 N/mm ²	suitable only under restricted conditions	7 m/min	M
CuZn	suitable only under restricted conditions	22 m/min	N
Oil	suitable		
wet maximum	suitable		
wet minimum	suitable		