

Garant

GARANT Master Form Steel fluteless machine tap with oil grooves Left-hand thread HSS-E-PM Form C 6HX, TiAlN, M-LH: M16



Order data

Order number	139255 M16
GTIN	4062406383824
Item class	11I

Description

Version:

The latest generation of **high-performance fluteless taps**, specially developed for **use in steel materials**.

- **Optimised polygon geometry for a lower torque.**
- **Multi-layer HIPIMS coating for high wear resistance.**
- **HSS-E-PM substrate for exceptional process reliability.**

DIN 2174 (\approx **DIN 371** \leq M10; \approx **DIN 376** \geq M12).

Tolerance class: ISO 2X 6HX

Thread pitch: 2 mm

Overall length L: 110 mm

Shank \varnothing D_s: 12 mm

Shank square □: 9 mm

Tapping hole \varnothing guide value: 15.1 mm

Technical description

Number of cutting edges Z	8
Number of clamping slots	8
Tolerance class	ISO 2X 6HX
Thread \varnothing	16 mm
Shank \varnothing D _s	12 mm
Series	GARANT Master

Overall length L	110 mm
Tapping hole Ø guide value	15.1 mm
Thread size	M16 LH
Thread depth	48 mm
Thread pitch	2 mm
Shank square □	9 mm
Coating	TiAlN
Thread type	M-LH
Flank angle	60 °
Tool material	HSS E PM
Standard	DIN 2174
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for blind holes
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Colour ring	without
Type of product	Fluteless tap

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable	38 m/min	N
Steel < 500 N/mm ²	suitable	37 m/min	P
Steel < 750 N/mm ²	suitable	35 m/min	P
Steel < 900 N/mm ²	suitable	27 m/min	P
Steel < 1100 N/mm ²	suitable	18 m/min	P

Steel < 1400 N/mm ²	suitable	12 m/min	P
INOX < 900 N/mm ²	suitable	12 m/min	M
INOX > 900 N/mm ²	suitable	7 m/min	M
CuZn	suitable only under restricted conditions	22 m/min	N
Oil	suitable		
wet maximum	suitable		
wet minimum	suitable		