

Garant

GARANT Master Form Steel fluteless machine tap with oil grooves HSS-E-PM Form C 6GX, TiAlN, M: M5



Order data

Order number	139205 M5
GTIN	4062406383558
Item class	111

Description

Version:

The latest generation of **high-performance fluteless taps**, specially developed for **use in steel materials**.

- **Optimised polygon geometry for a lower torque.**
- **Multi-layer HIPIMS coating for high wear resistance.**
- **HSS-E-PM substrate for exceptional process reliability.**

DIN 2174 (\approx DIN 371 \leq M10; \approx DIN 376 \geq M12).

Tolerance class: ISO 3X/6GX.

Application:

For components which are **galvanised**, or shrink slightly when hardened.

Tolerance class: ISO 3X 6GX

Thread pitch: 0.8 mm

Overall length L: 70 mm

Shank $\varnothing D_s$: 6 mm

Shank square \square : 4.9 mm

Tapping hole \varnothing guide value: 4.65 mm

Technical description

Thread depth	15 mm
Shank $\varnothing D_s$	6 mm
Tolerance class	ISO 3X 6GX
Number of clamping slots	5
Number of cutting edges Z	5

Tapping hole Ø guide value	4.65 mm
Thread size	M5
Series	GARANT Master
Overall length L	70 mm
Thread pitch	0.8 mm
Shank square □	4.9 mm
Thread Ø	5 mm
Coating	TiAlN
Thread type	M
Flank angle	60°
Tool material	HSS E PM
Standard	DIN 2174
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for blind holes
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Colour ring	without
Type of product	Fluteless tap

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable	38 m/min	N
Steel < 500 N/mm ²	suitable	37 m/min	P
Steel < 750 N/mm ²	suitable	35 m/min	P
Steel < 900 N/mm ²	suitable	27 m/min	P

Steel < 1100 N/mm ²	suitable	18 m/min	P
Steel < 1400 N/mm ²	suitable	12 m/min	P
INOX < 900 N/mm ²	suitable	12 m/min	M
INOX > 900 N/mm ²	suitable	7 m/min	M
CuZn	suitable	22 m/min	N
Oil	suitable		
wet maximum	suitable		
wet minimum	suitable		