

Garant

GARANT Master Form Steel fluteless machine tap with oil grooves HSS-E-PM Form C 7GX, TiAlN, M: M8



Order data

Order number	139207 M8
GTIN	4062406383657
Item class	111

Description

Version:

The latest generation of **high-performance fluteless taps**, specially developed for **use in steel materials**.

- **Optimised polygon geometry for a lower torque.**
- **Multi-layer HIPIMS coating for high wear resistance.**
- **HSS-E-PM substrate for exceptional process reliability.**

DIN 2174 (≈ DIN 371 ≤ M10; ≈ DIN 376 ≥ M12).

Tolerance class: 7GX.

Application:

For components which are **galvanised**, or shrink slightly when hardened.

Tolerance class: 7GX

Thread pitch: 1.25 mm

Overall length L: 90 mm

Shank Ø D_s: 8 mm

Shank square □: 6.2 mm

Tapping hole Ø guide value: 7.45 mm

Technical description

Overall length L	90 mm
Number of cutting edges Z	5
Shank square □	6.2 mm
Tapping hole Ø guide value	7.45 mm
Thread size	M8

Number of clamping slots	5
Shank $\varnothing D_s$	8 mm
Thread pitch	1.25 mm
Thread depth	24 mm
Series	GARANT Master
Thread \varnothing	8 mm
Tolerance class	7GX
Coating	TiAlN
Thread type	M
Flank angle	60°
Tool material	HSS E PM
Standard	DIN 2174
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for blind holes
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Colour ring	without
Type of product	Fluteless tap

User data

	Suitability	V_c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	38 m/min	N
Steel < 500 N/mm ²	suitable	37 m/min	P
Steel < 750 N/mm ²	suitable	35 m/min	P
Steel < 900 N/mm ²	suitable	27 m/min	P

Steel < 1100 N/mm ²	suitable	18 m/min	P
Steel < 1400 N/mm ²	suitable	12 m/min	P
INOX < 900 N/mm ²	suitable	12 m/min	M
INOX > 900 N/mm ²	suitable	7 m/min	M
CuZn	suitable	22 m/min	N
Oil	suitable		
wet maximum	suitable		
wet minimum	suitable		