

Garant
GARANT Diabolo solid carbide copy slot drill, TiAlN, Ø Dc × L1: 0,5X3mm

Order data

Order number	207377 0,5X3
GTIN	4062406387648
Item class	11X

Description
Version:
GARANT Diabolo:

Special geometry, coating and carbide **for hard machining in the high-performance field.**

Suitable even for **machining electrolytic copper.**

Recess angle $\alpha = 16^\circ$.

Extra-sturdy shank for achieving longer tool life.

Tolerances:

- **Corner radius: Radius contour = 0 / -0.005 mm.**
- **Neck Ø: D₁ = 0 / -0.01 mm.**

Note:

At greater tool overhang lengths, use a reduced value for a_p!
values for:

copying: $a_p = 0.05 \times D \times a_{p, \text{korr}}$

To calculate the feed rate vf please use the actual speed of the machine (the maximum possible speed)! e.g: $vf = 18000 \text{ [rpm]} \times fz \text{ [mm/Z]} \times z$

Technical description

Recess Ø D ₁	0.47 mm
Flute length L _c	0.4 mm
Feed f _z for copy milling in steel < 65 HRC	0.018 mm
Overall length L	54 mm
Cutting edge Ø D _c	0.5 mm
Helix angle	25 degrees

Shank $\varnothing D_s$	6 mm
Correction factor $a_{p\text{ corr}}$	0.9
Corner radius R_1	0.25 mm
No. of teeth Z	2
Overhang length L_1 incl. recess	3 mm
Series	Diabolo
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	H
Tolerance nominal \varnothing	0 / -0,005
Direction of infeed	horizontal, oblique and vertical
Cutting width a_e for milling operation	0.05xD for copy milling
Shank	DIN 6535 HA to h5
Through-coolant	no
Colour ring	red
Type of product	Ball-nosed slot drill

User data

	Suitability	V_c	ISO code
Steel < 750 N/mm ²	suitable only under restricted conditions	200 m/min	P
Steel < 900 N/mm ²	suitable only under restricted conditions	200 m/min	P
Steel < 1100 N/mm ²	suitable	190 m/min	P
Steel < 1400 N/mm ²	suitable	170 m/min	P
Steel < 50 HRC	suitable	120 m/min	H
Steel < 55 HRC	suitable	100 m/min	H
Steel < 60 HRC	suitable	72 m/min	H

Steel < 65 HRC	suitable	55 m/min	H
Steel < 67 HRC	suitable	50 m/min	H
Steel < 70 HRC	suitable	45 m/min	H
INOX < 900 N/mm ²	suitable	90 m/min	M
INOX > 900 N/mm ²	suitable	80 m/min	M
CuZn	suitable	140 m/min	N
wet maximum	suitable only under restricted conditions		
wet minimum	suitable only under restricted conditions		
dry	suitable		
Air	suitable		