

Garant
GARANT Diabolo solid carbide copy slot drill, TiAlN, Ø Dc × L1: 1,5X10mm

Order data

| | |
|--------------|---------------|
| Order number | 207377 1,5X10 |
| GTIN | 4062406387938 |
| Item class | 11X |

Description
Version:
GARANT Diabolo:

Special geometry, coating and carbide **for hard machining in the high-performance field.**

Suitable even for **machining electrolytic copper.**

Recess angle $\alpha = 16^\circ$.

Extra-sturdy shank for achieving longer tool life.

Tolerances:

- **Corner radius: Radius contour = 0 / -0.005 mm.**
- **Neck Ø: D₁ = 0 / -0.01 mm.**

Note:

At greater tool overhang lengths, use a reduced value for a_p!

values for:

copying: $a_p = 0.05 \times D \times a_{p, \text{corr}}$

To calculate the feed rate vf please use the actual speed of the machine (the maximum possible speed)! e.g: $vf = 18000 \text{ [rpm]} \times fz \text{ [mm/Z]} \times z$

Technical description

| | |
|---|------------|
| Corner radius R ₁ | 0.75 mm |
| Helix angle | 30 degrees |
| Shank Ø D _s | 6 mm |
| Overall length L | 54 mm |
| Overhang length L ₁ incl. recess | 10 mm |
| Correction factor a _{p, corr} | 0.9 |

| | |
|---|----------------------------------|
| Recess $\varnothing D_1$ | 1.44 mm |
| Cutting edge $\varnothing D_c$ | 1.5 mm |
| Feed f_z for copy milling in steel < 65 HRC | 0.022 mm |
| No. of teeth Z | 2 |
| Flute length L_c | 1.2 mm |
| Series | Diabolo |
| Coating | TiAlN |
| Tool material | Solid carbide |
| Standard | Manufacturer's standard |
| Type | H |
| Tolerance nominal \varnothing | 0 / -0,005 |
| Direction of infeed | horizontal, oblique and vertical |
| Cutting width a_e for milling operation | 0.05xD for copy milling |
| Shank | DIN 6535 HA to h5 |
| Through-coolant | no |
| Colour ring | red |
| Type of product | Ball-nosed slot drill |

User data

| | Suitability | V_c | ISO code |
|--------------------------------|---|-----------|----------|
| Steel < 750 N/mm ² | suitable only under restricted conditions | 200 m/min | P |
| Steel < 900 N/mm ² | suitable only under restricted conditions | 200 m/min | P |
| Steel < 1100 N/mm ² | suitable | 190 m/min | P |
| Steel < 1400 N/mm ² | suitable | 170 m/min | P |
| Steel < 50 HRC | suitable | 120 m/min | H |
| Steel < 55 HRC | suitable | 100 m/min | H |
| Steel < 60 HRC | suitable | 72 m/min | H |

| | | | |
|------------------------------|---|-----------|---|
| Steel < 65 HRC | suitable | 55 m/min | H |
| Steel < 67 HRC | suitable | 50 m/min | H |
| Steel < 70 HRC | suitable | 45 m/min | H |
| INOX < 900 N/mm ² | suitable | 90 m/min | M |
| INOX > 900 N/mm ² | suitable | 80 m/min | M |
| CuZn | suitable | 140 m/min | N |
| wet maximum | suitable only under restricted conditions | | |
| wet minimum | suitable only under restricted conditions | | |
| dry | suitable | | |
| Air | suitable | | |