

BENNING**Voltage tester DUSPOL®, Device type: ANALOG****Order data**

Order number	473106 ANALOG
GTIN	4067263133025
Item class	47A

Description**Version:**

Two-pole voltage tester with VDE kitemark. Shockproof, dustproof body. Protected against sprayed water, with rubberised gripping surfaces.

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Application:

Suitable for manual crafts, and for working on electrical systems, industrial systems, maintenance, servicing (troubleshooting), For professional multi-stage voltage and polarity testing, **with load switching (30 mA RCB trip by push button)**. Approved for voltage testing on **systems up to 1000 V**. Suitable for working on photovoltaic and wind turbine installations and hybrid vehicles.

Standard:

DIN EN 61243-3, VDE 0682-401:2015

Supplied with:

1 pc. voltage tester No. 473105 ANALOG or DIGITAL.

1 pc. carrying case No. 473336 B.

Technical description

Display range AC	12 - 1000 V
Display range DC	12 - 1000 V
Overvoltage category	CAT III 1000 V; CAT IV 600 V
Vibration alarm	yes
Phase testing	LCD
Calibration	I1
Three phase sequence testing	LCD
IP Index of Protection	IP 65
Display	plunge coil (illuminated) / LED
Manufacturer's designation	ANALOG
Polarity testing	LED
electrical insulation	VDE 1000 V
Type of product	Voltage tester

Services

CalibrationVoltage tester Type S	027120 S
DAkkS calibrationVoltage tester Type S	027160 S

Accessories

Voltage testerDUSPOL® Device type ANALOG	473105 ANALOG
Duspol carrying case Type B	473336 B