


Garant**ZCMX 09T302, Grade: HBZ310**

Order data

Order number	268437 HBZ310
GTIN	4062406392673
Item class	21E

Technical description

Tool material	Carbide
Corner radius	0.4 mm
Cutting speed v_c main application	200 - 600 m/min
Number of changes/inserts	2
Cutting depth a_p	0.2 - 4 mm
Feed rate f when turning	0.05 - 0.4 mm
Main application	N
Feed rate f when drilling	0.03 - 0.3 mm
Coating	PVD
ISO code indexable insert	ZCMX 10T304
Grade	HBZ310
Cutting conditions	continuous

suitable for tool dia. D_c	18 mm
Type of product	Indexable insert for turning