

Garant**Bench vice, Jaw width: 180mm****Order data**

Order number	967100 180
GTIN	4062406393267
Item class	91J

Description**Version:****Entirely of forged steel – guaranteed unbreakable.**

Slides forward on opening. With pipe clamping jaws underneath the normal jaws. Powerful, CNC-machined precision spindle with rolled thread. Spindle and guides are protected from dirt. Large hardened anvil area for shaping and upsetting work. Double adjustable guide. With solid, surface-hardened jaws (not interchangeable).

Callout:

Impact absorber washers.

Embossed measuring scale.

Guide setting: Internal hexagon screw with brass thrust washers – runs very easily.

Strong pipe jaws.

Advantage:

- **Tightening bar with impact-absorbing washers at both ends no irritating noise when the bar falls through.**
- **Long-pitch thread spindle for quick opening and closing.**
- **Interchangeable tightening bar.**
- **Opening scale embossed into slide.**

Supplied with:

Fasteners for attachment to the workbench.

Note:

For suitable height adjuster see No. 967520.

Technical description

Pipe jaws clamp pipes with outer Ø	3/4 – 3.1/2 in
Material	Drop forged steel
Clamping depth	110 mm
Opening direction	opens to the front
Weight	27 kg
Jaw width	180 mm
Jaw capacity	220 mm
Type of product	Machinist's vice