

**Modular counterboring set in a wooden stand, Size / shank size: 0MK1****Order data**

Order number	156700 0MK1
GTIN	4033591011571
Item class	16C

**Description****Version:**

Set of holders, counterbores, and pilots for machining the most common bore Ø.

**Application:**

**For DIN counterbores**, as well as appropriate pilot / counterbore combinations for stepped holes or non-standard counterbores.

**Content:**

1× each counterbore No. 156730: 8.5; 9.5; 10.5; 11.5; 13.5; 16.5

1× each pilot No. 156750: 4; 4.5; 5; 5.5; 6; 6.5; 7; 7.5; 8; 8.5; 9; 9.5; 10; 10.5

1× each holder No. 156720 with shank: MT1

**Note:**

Modular counterboring sets also available in HSS with optional TIN coating and brazed-on carbide tips with form "T" ISO inserts.

Through-coolant: yes

Number of cutting edges Z: 2

Number of cutting edges Z: 2

Counterbore range: 8.5 - 16.5 mm

**Technical description**

Counterbore range	8.5 - 16.5 mm
-------------------	---------------

Number of cutting edges Z	2
Tool material	HSS
Through-coolant	yes
Type of product	Counterbore

---

## Accessories

Modular counterboring system holder Size / shank size OMK1	156720 OMK1
---	-------------