

**Garant**
**Machine tap for cast iron, nitrided, M: M10**

**Order data**

Order number	132500 M10
GTIN	4045197071804
Item class	11H

**Description**
**Version:**
**With straight flutes and short chamfer lead (2 – 3 turns).**
**Callout:**

4 cutting edges (from size M5).

4 flutes (from size M5).

Particularly wear resistant due to nitrided surface (13 2500).

Thread type: M

Tool material: HSS E

Standard: DIN 371

Tolerance class: ISO 2X 6HX

Thread pitch: 1.5 mm

Overall length L: 100 mm

 Shank  $\varnothing$  D<sub>s</sub>: 10 mm

 Shank square  $\square$ : 8 mm

 Tapping hole  $\varnothing$ : 8.5 mm

**Technical description**

Thread pitch	1.5 mm
Tapping hole $\varnothing$	8.5 mm
Number of cutting edges Z	4
Thread $\varnothing$	10 mm
Number of clamping slots	4
Standard	DIN 371

Shank $\varnothing D_s$	10 mm
Overall length L	100 mm
Shank square $\square$	8 mm
Tolerance class	ISO 2X 6HX
Tool material	HSS E
Thread depth	30 mm
Thread type	M
Thread size	M10
Coating	nitrided
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3xD for blind holes
Application for type of drilling	up to 3xD for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	white
Type of product	Tap

## User data

	Suitability	$V_c$	ISO code
GG	suitable	13 m/min	K
GGG	suitable only under restricted conditions	9 m/min	K
wet maximum	suitable		
dry	suitable only under restricted conditions		

