

Garant
Brass machine tap short, uncoated, M: M10

Order data

| | |
|--------------|---------------|
| Order number | 132600 M10 |
| GTIN | 4045197072160 |
| Item class | 11H |

Description
Version:
With 6° flute angle and short chamfer lead (2 – 3 turns).
Application:

For use as machine tap or for cleaning existing threads by hand.

Thread type: M

Tool material: HSS E

Standard: DIN 352

Tolerance class: ISO 2 6H

Thread pitch: 1.5 mm

Overall length L: 70 mm

 Shank $\varnothing D_s$: 7 mm

 Shank square \square : 5.5 mm

 Tapping hole \varnothing : 8.5 mm

Technical description

| | |
|----------------------------|---------|
| Number of clamping slots | 3 |
| Number of cutting edges Z | 3 |
| Thread \varnothing | 10 mm |
| Tapping hole \varnothing | 8.5 mm |
| Thread pitch | 1.5 mm |
| Standard | DIN 352 |
| Shank $\varnothing D_s$ | 7 mm |

| | |
|----------------------------------|-----------------------------------|
| Overall length L | 70 mm |
| Shank square □ | 5.5 mm |
| Tolerance class | ISO 2 6H |
| Tool material | HSS E |
| Thread depth | 30 mm |
| Thread type | M |
| Thread size | M10 |
| Coating | uncoated |
| Flank angle | 60° |
| Thread standard | DIN 13 |
| Taper lead form | C |
| Shank | Plain shank with h9 |
| Through-coolant | no |
| Application for type of drilling | up to 3×D for blind holes |
| Application for type of drilling | up to 3×D for through holes |
| Cutting direction | right-hand |
| Type of threading tool | Machine tap for dynamic machining |
| Colour ring | white |
| Type of product | Tap |

User data

| | Suitability | V _c | ISO code |
|-------|---|----------------|----------|
| GG(G) | suitable only under restricted conditions | 10 m/min | K |
| CuZn | suitable | 13 m/min | N |
| dry | suitable | | |