

**Garant****Shoulder mill 90°, with bore, Ø D / number of teeth Z: 63/6mm****Order data**

Order number	215101 63/6
GTIN	4062406394806
Item class	210

**Description****Version:**

Robust shoulder milling cutter. Insert seats enclose the inserts on several sides for stable machining conditions.

For use in combination with indexable insert 215117 UNI as a **high feed rate indexable face mill**.

**Application:**

With double-sided 3-edge inserts XNEX0806.. or single-sided 3-edge inserts XNEX0806.. **High feed rate**.

**Note:**

GARANT torque screwdriver TQ No. **211750 size 3.8** with bit No. **674252 size 15IP**.

**Technical description**

Overall length $L_{tot}$	40 mm
Mounting bore $\varnothing$	22 mm
Pack of insert screws	219798 1 (15IP; 3.8 Nm)
Cutting edge $\varnothing D_c$	63 mm

Number of cutting edges Z	6
suitable indexable insert	XNEX 0806..
maximum cutting depth $a_{p\max}$	4 mm
Shank type	with bore
Setting angle $\kappa$	90 degrees
Milling application	End milling
Spacing of the cutters	unequal spacing
Through-coolant	yes
Tool exchange	PowerCard
Type of product	End / face mill

## Accessories

Set of insert screws 10 pieces Type 1	219798 1
---------------------------------------	----------