



Indexable milling cutter 90°, with bore, Ø D: 40/4mm



Order data

Order number	215717 40/4
GTIN	4062406394974
Item class	220

Description

Version:

Indexable face mill with irregular pitch for very smooth cutting.
Without through-coolant feed.

Note:

Use GARANT torque screwdriver TQ No. **211750 size 5.0** with bit No. **674252 size 15IP**.

Technical description

suitable indexable insert	AP.. 16..
Overall length L_{tot}	40 mm
Mounting bore \varnothing	16 mm
Number of cutting edges Z	4
Cutting edge $\varnothing D_c$	40 mm
Pack of insert screws	219812 (15IP; 5.0 Nm)
Shank type	with bore

Setting angle κ	90 degrees
Milling application	End milling
Spacing of the cutters	unequal spacing
Type of product	End / face mill

Accessories

Set of insert screws 10-piece	219812
-------------------------------	--------