



Lubricating grease LINOMAX plus, Weight: 500g



Order data

| | |
|--------------|---------------|
| Order number | 313190 500 |
| GTIN | 2050002053021 |
| Item class | 30N |

Description

Version:

Partially synthetic high-performance grease for regular lubrication of manual chucks and heavy-duty chucks. High bonding capability and water resistance permit constant clamping forces with regular application. The special grease adheres even in the event of rotation in the lathe chuck.

Feature:

Density 1.33 g/cm³.

Consistency class 2.

Coefficient of friction 0.09.

Shelf life 3 years.

Supplied with:

500 g grease cartridge.

Note:

Note the dimensions of the grease gun! Cartridge dimensions: Ø 55 mm × 237 mm.

Technical description

| | |
|-----------------------------|--------------|
| Shape | Paste |
| Operating temperature range | -25 - 120 °C |
| Flashpoint | 174 °C |
| Colour | beige |
| Type of product | Lubricant |

