

**Garant**
**Solid carbide T-slot cutter, TiAlN, Ø DC × LC d11 × d11: 12,5X6mm**

**Order data**

Order number	208026 12,5X6
GTIN	4062406397166
Item class	11X

**Description**
**Version:**

**With new high-performance coating** for very long tool life. The mill cuts on all three sides. Due to alternate set teeth (staggered).

**Note:**

Suitable for milling T-slots according to DIN 650.

Feed at 50 %  $f_z$  until full engagement.

**Successor product to No. 208032.**

**Technical description**

Shank Ø $D_s$	10 mm
Recess Ø $D_1$	5 mm
for T-slots DIN 650	6 mm
Cutting edge Ø $D_c$	12.5 mm
No. of teeth Z	6
Type	N
Corner chamfer width at 45°	0.2 mm
Feed $f_z$ in steel < 900 N/mm <sup>2</sup>	0.033 mm
Overall length L	57 mm
Flute length $L_c$	6 mm

Coating	TiAlN
Tool material	Solid carbide
Standard	DIN 851
Milling profile	staggered teeth
Tolerance nominal $\varnothing$	d11
Helix angle	10 degrees
Direction of infeed	horizontal
Shank	DIN 6535 HB to h6
Through-coolant	no
Shank tolerance	h6
Corner chamfer angle	45 degrees
Colour ring	green
Type of product	Slot milling cutter

## User data

	Suitability	$V_c$	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable	105 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	90 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	90 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	80 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable only under restricted conditions	60 m/min	P
Uni	suitable		
wet maximum	suitable		