

Garant
Solid carbide side milling cutter HPC, TiAlN, $\varnothing \times \text{width} \pm 0.1 \times k11$: 63X10mm

Order data

Order number	185015 63X10
GTIN	4062406397487
Item class	11V

Description
Version:

Precision solid carbide side milling cutters in the HPC machining range. **With new high-performance coating** for very long tool life.

Use as a set: Cutters with the same \varnothing and same number of teeth can be combined as a set and adjusted to the required width. Since the cutters have no raised bore collar, the staggered teeth mesh with each other.

2-piece sets are particularly economical. By reversing the side milling cutters, both side edges of each cutter can be used.

Note:

- **Do not clamp the cutters in a set without a sufficiently thick arbor spacer ring, otherwise the cutters will be damaged.**
- **See Product Group 30 for suitable arbor spacer rings.**
- **Slots milled from solid: f_z for $a_e = 0.1 \times D$.**

Successor product to No. 185010.

Technical description

Collar thickness $b \pm 0.1$	7.2 mm
------------------------------	--------

Bore \varnothing H6 d ₁	22 mm
No. of teeth Z	14
Capability of combining 2 cutters of the same width A/B	10 mm
Tooth height Zh	11.5 mm
Cutting edge \varnothing D _c	63 mm
Shank type	with bore
Collar \varnothing d ₂ ±1	40 mm
Feed f _z in steel < 900 N/mm ²	0.06 mm
Cutting width	10 mm
Capability of combining 2 cutters of the same width, results in overall width E	18.5 - 19.8 mm
Coating	TiAlN
Tool material	Solid carbide
Standard	DIN 885 A
Type	N
Tolerance nominal \varnothing	± 0.1
Cutting width a _e for milling operation	Full slot cutting depth 1×D
Machining strategy	HPC
Through-coolant	no
Colour ring	without
Type of product	Side milling cutter

User data

	Suitability	V _c	ISO code
Alu plastics	suitable	280 m/min	N
Aluminium (short chipping)	suitable	280 m/min	N
Alu > 10% Si	suitable	200 m/min	N
Steel < 500 N/mm ²	suitable	120 m/min	P

Steel < 750 N/mm ²	suitable	110 m/min	P
Steel < 900 N/mm ²	suitable	100 m/min	P
Steel < 1100 N/mm ²	suitable	90 m/min	P
Steel < 1400 N/mm ²	suitable	75 m/min	P
INOX < 900 N/mm ²	suitable	45 m/min	M
GG(G)	suitable	70 m/min	K
CuZn	suitable	300 m/min	N
Oil	suitable only under restricted conditions		
wet maximum	suitable		