

Garant
Solid carbide dovetail milling cutter Form C 45°, TiAlN, Ø js14 DC: 12mm

Order data

Order number	208028 12
GTIN	4062406397685
Item class	11X

Description
Version:

With new high-performance coating for very long tool life.

Angular tolerance ± 8 arc minutes.

Note:

Successor product to No. 208035.

For milling dovetails in tool making and machine building.

Feed at 50 % f_z until full engagement.

Technical description

Shape	C
Overall length L	55 mm
Flute length L_c	3 mm
No. of teeth Z	6
Shank $\varnothing D_s$	10 mm
Recess $\varnothing D_1$	5 mm
Feed f_z in steel $< 900 \text{ N/mm}^2$	0.04 mm
Cutting edge $\varnothing D_c$	12 mm
Coating	TiAlN
Tool material	Solid carbide

Standard	DIN 1833
Type	N
Tolerance nominal \varnothing	js14
Direction of infeed	horizontal
Shank	DIN 6535 HB to h6
Through-coolant	no
Shank tolerance	h6
Corner chamfer angle	45 degrees
Colour ring	green
Type of product	Dovetail milling cutter

User data

	Suitability	V_c	ISO code
Steel < 500 N/mm ²	suitable	105 m/min	P
Steel < 750 N/mm ²	suitable	90 m/min	P
Steel < 900 N/mm ²	suitable	90 m/min	P
Steel < 1100 N/mm ²	suitable	80 m/min	P
Steel < 1400 N/mm ²	suitable only under restricted conditions	60 m/min	P
Uni	suitable		
wet maximum	suitable		