

Garant
Boring bar carbide, right-hand, Shank \varnothing / insert size: 20/11 mm

Order data

Order number	261112 20/11
GTIN	4062406398026
Item class	21T

Technical description

Setting angle κ	142 degrees
Pack of insert screws	269028 7
Overall length L	250 mm
Minimum pre-drill $\varnothing D_{\min}$	24 mm
ISO code toolholder	E20S SVJBR/L 11
Head length L_1	38 mm
Clamping height L_2	19 mm
Neck width L_4	11 mm
Centre offset L_3	2 mm
Insert size	11 mm
suitable indexable insert	VB.. 1103..
Shank $\varnothing D_s$	20 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 7	269028 7
-----------------------------	----------