

**Garant****Hand tap set, left-hand thread, uncoated, M-LH: M10****Order data**

Order number	130460 M10
GTIN	4062406398132
Item class	11G

**Description****Version:**

Set of three, **consisting of taper, second, and plug tap.**

**Application:**

For metric left-hand thread to DIN13.

Thread type: M-LH

Tool material: HSS

Standard: DIN 352

Tolerance class: ISO 2 6H

Thread pitch: 1.5 mm

Overall length L: 70 mm

Shank  $\varnothing D_s$ : 7 mm

Shank square  $\square$ : 5.5 mm

Tapping hole  $\varnothing$ : 8.5 mm

**Technical description**

Standard	DIN 352
Thread size	M10
Number of cutting edges Z	3
Number of clamping slots	3
Tolerance class	ISO 2 6H

Shank $\varnothing D_s$	7 mm
Tapping hole $\varnothing$	8.5 mm
Thread pitch	1.5 mm
Overall length L	70 mm
Thread $\varnothing$	10 mm
Tool material	HSS
Thread depth	30 mm
Shank square $\square$	5.5 mm
Thread type	M-LH
Coating	uncoated
Flank angle	60 °
Thread standard	DIN 13
Taper lead form	D
Taper lead form	C
Taper lead form	A
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for blind holes
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Hand tap
Colour ring	without
Type of product	Tap

## User data

	Suitability	$V_c$	ISO code
Alu plastics	suitable only under restricted conditions		

Aluminium (short chipping)	suitable only under restricted conditions
Alu > 10% Si	suitable only under restricted conditions
Steel < 500 N/mm <sup>2</sup>	suitable
Steel < 750 N/mm <sup>2</sup>	suitable
Steel < 900 N/mm <sup>2</sup>	suitable
GG(G)	suitable only under restricted conditions
Uni	suitable only under restricted conditions
Oil	suitable
dry	suitable only under restricted conditions