

**Garant**
**Hand tap set, left-hand thread, uncoated, M-LH: M8**

**Order data**

Order number	130460 M8
GTIN	4062406398125
Item class	11G

**Description**
**Version:**

Set of three, **consisting of taper, second, and plug tap.**

**Application:**

For metric left-hand thread to DIN13.

Thread type: M-LH

Tool material: HSS

Standard: DIN 352

Tolerance class: ISO 2 6H

Thread pitch: 1.25 mm

Overall length L: 56 mm

Shank  $\varnothing D_s$ : 6 mm

Shank square  $\square$ : 4.9 mm

Tapping hole  $\varnothing$ : 6.8 mm

**Technical description**

Number of cutting edges Z	3
Shank $\varnothing D_s$	6 mm
Tapping hole $\varnothing$	6.8 mm
Number of clamping slots	3
Standard	DIN 352

Thread size	M8
Tool material	HSS
Thread depth	24 mm
Shank square □	4.9 mm
Thread pitch	1.25 mm
Thread type	M-LH
Tolerance class	ISO 2 6H
Overall length L	56 mm
Thread Ø	8 mm
Coating	uncoated
Flank angle	60 °
Thread standard	DIN 13
Taper lead form	D
Taper lead form	C
Taper lead form	A
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for blind holes
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Hand tap
Colour ring	without
Type of product	Tap

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu plastics	suitable only under restricted conditions		

Aluminium (short chipping)	suitable only under restricted conditions
Alu > 10% Si	suitable only under restricted conditions
Steel < 500 N/mm <sup>2</sup>	suitable
Steel < 750 N/mm <sup>2</sup>	suitable
Steel < 900 N/mm <sup>2</sup>	suitable
GG(G)	suitable only under restricted conditions
Uni	suitable only under restricted conditions
Oil	suitable
dry	suitable only under restricted conditions