

Garant

GARANT Master Alu solid carbide torus cutter HPC, DLC, Ø h6 DC / RS1: 12/1,0mm



Order data

Order number	206264 12/1,0
GTIN	4062406398651
Item class	11X

Description

Version:

Eccentric relief ground, additionally polish ground in the flutes for outstanding chip evacuation in long-chipping non-ferrous materials.

Very high feed rates when plunging vertically. Ramping capability up to 45°.

Tolerances:

· Corner radius

RS₁ = 0.5 tolerance ±0.02.

RS₁ > 0.5 – 1.5 tolerance ±0.03.

RS₁ > 1.5 tolerance ±0.05.

Application:

Particularly suitable for finishing work.

Technical description

No. of teeth Z	4
Recess Ø D ₁	11 mm
Shank Ø D _s	12 mm
Flute length L _c	49 mm
Overall length L	100 mm
Overhang length L ₁ incl. recess	60 mm
Feed f _z for side milling in short-chipping aluminium	0.06 mm
Shank	DIN 6535 HA to h6

Cutting edge $\varnothing D_c$	12 mm
Balance quality with shank	G 2.5 with HA
Corner radius R_1	1 mm
Series	Master Alu
Coating	DLC
Tool material	Solid carbide
Standard	DIN 6527
Type	W
Tolerance nominal \varnothing	e8
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Direction of infeed	horizontal, oblique and vertical
Cutting width a_e for milling operation	Full slot cutting depth $1 \times D$
Through-coolant	no
Machining strategy	HPC
Colour ring	yellow
Type of product	Torus cutter

User data

	Suitability	V_c	ISO code
Aluminium	Suitable	500 m/min	N
Aluminium (short chipping)	Suitable	450 m/min	N
Alu > 10% Si	Suitable	400 m/min	N
PMMA acrylic	Suitable	180 m/min	N
PE-HD	Suitable	140 m/min	N
PA 66	Suitable	180 m/min	N
PEEK	Suitable	130 m/min	N
PF 31	Suitable	110 m/min	N

PVDF GF20	Suitable	160 m/min	N
POM GF25	Suitable	140 m/min	N
PA 66 GF30	Suitable	120 m/min	N
PEEK GF30	Suitable	140 m/min	N
PTFE CF25	Suitable	260 m/min	N
Honeycomb sandwich	suitable	260 m/min	N
Cu	Suitable	140 m/min	N
CuZn	Suitable	120 m/min	N
wet maximum	suitable		
wet minimum	Suitable only under restricted conditions		
dry	Suitable only under restricted conditions		
Air	Suitable		