



## Eccentric fixture clamp with knife edge, Thread M: M10



### Order data

|              |               |
|--------------|---------------|
| Order number | 370008 M10    |
| GTIN         | 4046368875849 |
| Item class   | 37M           |

### Description

#### Version:

- Requires only small space, so few interference contours.
- Clamping of workpieces of any shape.

Clamping washer of case-hardened steel with eccentric steel screw.

#### Supplied with:

1 pc. steel screw, 1 pc. clamping washer.

#### Note:

A hexagon L-wrench size 7 is required for clamp M 10!

### Technical description

|                           |         |
|---------------------------|---------|
| Clamping force            | 9 kN    |
| Thread length L           | 20 mm   |
| Eccentric travel $S_1$    | 1.6 mm  |
| Dimension A               | 10.2 mm |
| maximum tightening torque | 28 Nm   |

|                                  |                 |
|----------------------------------|-----------------|
| Washer height H                  | 9.6 mm          |
| Internal hexagon AF <sub>1</sub> | 7 mm            |
| Thread M                         | M10             |
| Claw plate Ø D <sub>1</sub>      | 20.6 mm         |
| Type of product                  | Eccentric clamp |