

Garant
Machine tap HSS-E-PM, DLC, M: M2,5

Order data

Order number	132610 M2,5
GTIN	4045197648778
Item class	11H

Description
Version:

With **the latest generation of sp²**.

Very sturdy design, with spiral point and special cutting edge geometry for copper materials.

For use with **emulsion** (fat content minimum 8%).

Thread type: M

Tool material: HSS E PM

Standard: DIN 371

Tolerance class: ISO 2 6H

Thread pitch: 0.45 mm

Overall length L: 50 mm

Shank $\varnothing D_s$: 2.8 mm

Shank square \square : 2.1 mm

Tapping hole \varnothing : 2.05 mm

Technical description

Thread \varnothing	2.5 mm
Tapping hole \varnothing	2.05 mm
Number of clamping slots	2
Thread pitch	0.45 mm
Number of cutting edges Z	2
Standard	DIN 371
Shank $\varnothing D_s$	2.8 mm

Overall length L	50 mm
Shank square □	2.1 mm
Tolerance class	ISO 2 6H
Tool material	HSS E PM
Thread depth	7.5 mm
Thread type	M
Thread size	M2.5
Coating	DLC
Flank angle	60 degrees
Thread standard	DIN 13
Taper lead form	CS
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	white
Type of product	Tap