

Garant**Centring mandrel, Type: 120/138****Order data**

Order number	360027 120/138
GTIN	4045197812810
Item class	310

Description**Version:**

The zero point clamping of the GARANT ZeroClamp system is an important function for modern production systems, especially in automated production. Thanks to a special contact interface, it ensures precise and reliable zero point repetition accuracy. The pneumatic clamping force of the system holds workpieces securely in the desired position, making it possible to change workpieces quickly and accurately without repositioning. This reduces the set-up effort and increases productivity. The zero point clamping of the GARANT ZeroClamp system is indispensable for efficient production processes. Find out more about the innovative technology from GARANT ZeroClamp and optimise your production.

Application:

Permits a quick approach to a point on the machine table and alignment of the clamping pot.

Suitable for:

Clamping pots size 120 and 138.

Technical description

Shank Ø	25 mm
Overall length	150 mm

Shaft length	50 mm
Series	ZeroClamp
Type of product	Centring mandrel