Garant

Fluteless machine tap with oil grooves HSS-E-PM Form C 6HX, TiN, M: M4



Order data

Order number	139178 M4
GTIN	4045197509116
Item class	11H

Description

Version:

DIN 2174 (\approx DIN 371 \leq M10; \approx DIN 376 \geq M12). With oil grooves; optimum lubrication effect even in deeper threads. Tolerance class: ISO 2X/6HX. The innovative polygon form permits a wide application spectrum. The multi-function layer structure achieves maximum service life even in high-tensile materials. Tolerance class: ISO 2X 6HX Thread pitch: 0.7 mm Overall length L: 63 mm Shank Ø D_s: 4.5 mm Shank square \Box : 3.4 mm Tapping hole Ø with guide value: 3.7 mm

Technical description

Thread pitch	0.7 mm
Number of clamping slots	4
Thread Ø	4 mm
Number of cutting edges Z	4
Shank Ø D _s	4.5 mm
Shank square 🗆	3.4 mm
Overall length L	63 mm
Tapping hole \varnothing with guide value	3.7 mm

Tolerance class	ISO 2X 6HX
Thread depth	12 mm
Thread size	M4
Coating	TiN
Thread type	Μ
Flank angle	60 degrees
Tool material	HSS E PM
Standard	DIN 2174
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for blind holes and through holes
Cutting direction	right-hand
Colour ring	green
Type of product	Fluteless tap