

Garant
Machine tap for synchronised spindles HSS-E-PM Form E, TiAlN, M: M6

Order data

Order number	132560 M6
GTIN	4045197585332
Item class	11H

Description
Version:

Sturdy design with shank to DIN 1835-B. Special geometry for use on machines with **synchronised spindle drives**. The tap is controlled by the synchronising spindle of the machine. **Special TiAlN coating for optimum tool life.** For use with **emulsion** (fat content minimum 8 %).

Also outstandingly suitable for **bainite cast iron (ADI)**.

Note:

For use on synchronised spindles, the **GARANT** quick-change tapping chuck **No. 338100 – 338121 with minimum length adjustment (MLA)** ensures maximum process reliability.

Thread type: M

Tool material: HSS E PM

Standard: Manufacturer's standard

Tolerance class: ISO 2X 6HX

Thread pitch: 1 mm

Overall length L: 80 mm

Shank $\varnothing D_s$: 6 mm

Shank square \square : 4.9 mm

Tapping hole \varnothing : 5 mm

Technical description

Thread pitch	1 mm
Tapping hole \varnothing	5 mm
Thread \varnothing	6 mm
Number of clamping slots	4

Number of cutting edges Z	4
Standard	Manufacturer's standard
Shank $\varnothing D_s$	6 mm
Overall length L	80 mm
Shank square \square	4.9 mm
Tolerance class	ISO 2X 6HX
Tool material	HSS E PM
Thread depth	15 mm
Thread type	M
Thread size	M6
Coating	TiAlN
Flank angle	60°
Thread standard	DIN 13
Taper lead form	E
Shank	DIN 1835 B with h6
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Application for type of drilling	up to 2.5×D for through holes
Cutting direction	right-hand
Shank tolerance	h6
Type of threading tool	Machine tap for synchronous machining
Colour ring	white
Type of product	Tap

User data

	Suitability	V_c	ISO code
GJS, ADI > 800N/mm ²	suitable	20 m/min	K
wet maximum	suitable		

wet minimum	suitable only under restricted conditions
Air	suitable only under restricted conditions