



Combination face mill adapter, HSK-A 63 A = 100, Spigot Ø d1: 22mm



Order data

Order number	306137 22
GTIN	4062406422585
Item class	32A

Description

Version:

With RFID/Balluffchip bore. HSK mating faces machined.
Balancing quality G 6.3 at 20000 rpm.

Application:

For clamping shell end mills and milling cutter heads with longitudinal or transverse groove.

Supplied with:

Incl. drive key, face mill drive ring, and lock screw No. 309860.

Optional extras:

Coolant tube No. 309880, socket wrench No. 309890, toggle spanner No. 309840, milling cutter lock screw for internal coolant supply No. 309861.

Note:

Internal cooling available only with suitable tightening screw No. 309861.

Technical description

Overhang dimension A	100 mm
Spigot Ø d ₁	22 mm
Spare drive ring No. 309870	22
External Ø D	40 mm
Milling mandrel length L ₄	31 mm
Suitable toggle spanner No. 309840	22

Milling mandrel length L ₃ with drive ring	19 mm
Spare milling cutter lock screw No. 309860 / 309861	22
Clamping Ø D ₁	22 mm
Adapter	HSK-A 63 A = 100
Arbor standard	DIN 69893
Arbor standard	ISO 12164-1
Arbor standard	DIN 69893
Shape	A
Balance quality G at rotational speed	G 6.3 at 20,000 rpm
Concentricity	≤ 6 µm
Machining strategy	HPC
Type of product	Milling cutter spigot

Accessories

Toggle spanner for mandrel Ø 22 mm	309840 22
Milling cutter lock screw for mandrel Ø 22 mm	309860 22
Face mill drive ring for mandrel Ø 22 mm	309870 22