


ER collet chuck mini / slim Form AD, SK 40 A = 100, for ER collet size: 16

Order data

Order number	300651 16
GTIN	4062406422301
Item class	32A

Description
Version:

Clamping nut fine balanced **for HSC**. ER11 through bored. Shanks hard turned (smooth cutting action!).

· **With Balluffchip bore as standard.**

Application:

For clamping tools with plain shank to DIN 6499.

Supplied with:

High speed ER mini nut No. 309650.

Optional extras:

ER collets No. 308881 – 309434, ER lock wrench No. 309740.

Pull studs (PS) No. 308600 – 308806. PS chuck key No. 308820; 308830.

Machining strategy: HSC

Clamping range: 0.5 - 10 mm

Overhang dimension A: 100 mm

External Ø D: 22 mm

Suitable chuck key No. 309740: 16

Technical description

Clamping range	0.5 - 10 mm
Usable length L _N	70 mm
Suitable chuck key No. 309740	16
External Ø D	22 mm

for ER collets	16 mm
Overhang dimension A	100 mm
Clamping $\varnothing D_1$	0.5-10 mm
Adapter	SK 40 A = 100
Arbor standard	ISO 7388-1
Shape	AD
Balance quality G at rotational speed	G 6.3 at 18,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HSC
Type of product	Collet chuck

Accessories

Pull stud Mori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
ER collet for machine taps with seal Nominal clamping $\varnothing d$ 4,5 mm	309402 4,5
ER collet set 10 pieces 1–10 mm with seal and spray nozzles	309165
ET collet with radial compensation for tapping and reaming Nominal clamping $\varnothing d$ 3 mm	309445 3
ER collet Nominal clamping $\varnothing d$ 5 mm	308901 5
ER chuck key 1/2 inch 25AF for ER collet chuck 16	309720 16
ER collet with seal and spray nozzles Nominal clamping $\varnothing d$ 7 mm	308922 7
ER collet Nominal clamping $\varnothing d$ 4 mm	308920 4
Pull stud Form A suitable for steep tapers 40	308600 40
ER collet Nominal clamping $\varnothing d$ 9 mm	308901 9
Wrench for pull studs ISO 7388 suitable for ISO taper size 40	308830 40
	309404 3,5

ER collet for machine taps with seal and spray nozzles
Nominal clamping \varnothing d 3,5 mm

ER collet Nominal clamping \varnothing d 2,5 mm	308901 2,5
ER collet for machine taps with seal and spray nozzles Nominal clamping \varnothing d 6 mm	309404 6
ER collet Nominal clamping \varnothing d 10 mm	308901 10
ER collet set 10 pieces 1–10 mm with seal	309164
ER collet with seal Nominal clamping \varnothing d 10 mm	308906 10
ER collet for machine taps with seal Nominal clamping \varnothing d 3,5 mm	309403 3,5
Pull stud sealed, form B suitable for steep tapers 40	308620 40
Pull stud, 18CrNiMo7 sealed, form B suitable for steep tapers 40	308615 40
ER collet for machine taps with seal Nominal clamping \varnothing d 2,8 mm	309402 2,8
ER collet with seal Nominal clamping \varnothing d 6 mm	308921 6
Torque insert for Pull studs to SO 7388 suitable for ISO taper size 40	308812 40
ER collet for machine taps with seal and spray nozzles Nominal clamping \varnothing d 8 mm	309404 8
ER collet with seal and spray nozzles Nominal clamping \varnothing d 9 mm	308922 9
ER collet Nominal clamping \varnothing d 8 mm	308920 8
ER collet Nominal clamping \varnothing d 2 mm	308901 2
Pull stud Hurco 90° with fit sealed suitable for steep tapers 40	308806 40
Wrench for ER Mini nuts for ER collet chuck 16	309740 16
Special pull stud with no internal thread sealed suitable for steep tapers 40	308720 40
ER collet for machine taps with seal Nominal clamping \varnothing d 2,8 mm	309403 2,8
ER collet set 10 pieces 1–10 mm	309160
ER collet Nominal clamping \varnothing d 5 mm	308920 5

Pull stud, 18CrNiMo7 Form A suitable for steep tapers 40	308605 40
Pull stud 45° sealed suitable for steep tapers 40	308760 40
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 7 mm	309404 7
ER chuck key 1/2 inch socket for ER collet chuck 40	309700 40
ER collet with seal Nominal clamping Ø d 4 mm	308906 4
ER collet Nominal clamping Ø d 6 mm	308920 6
ER collet for machine taps with seal Nominal clamping Ø d 4,5 mm	309403 4,5
Pull stud sealed suitable for steep tapers 40	308635 40
ER collet with seal Nominal clamping Ø d 9 mm	308921 9
ER collet with seal Nominal clamping Ø d 4 mm	308921 4
ER collet for machine taps with seal Nominal clamping Ø d 9 mm	309402 9
ER chuck key 1/2 inch socket for ER collet chuck 16	309700 16
ER collet Nominal clamping Ø d 3 mm	308901 3
ER collet with seal Nominal clamping Ø d 6 mm	308906 6
Hurco 45° pull stud with 4-mm bore and fit sealed suitable for steep tapers 40	308801 40
ER collet with seal Nominal clamping Ø d 3 mm	308906 3
ER collet for machine taps with seal Nominal clamping Ø d 4 mm	309403 4
Pull stud sealed, form B suitable for steep tapers 40	308650 40
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 4,5 mm	309404 4,5
ER collet Nominal clamping Ø d 3 mm	308920 3
ER collet with seal Nominal clamping Ø d 9 mm	308906 9
ER collet for machine taps with seal Nominal clamping Ø d 6 mm	309403 6
ER collet with seal Nominal clamping Ø d 7 mm	308906 7
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 5 mm	309445 5

ER collet Nominal clamping Ø d 9 mm	308920 9
ER collet with seal Nominal clamping Ø d 3 mm	308921 3
ER collet with seal Nominal clamping Ø d 5 mm	308921 5
Pull stud 90° sealed suitable for steep tapers 40	308795 40
Pull stud Mazak, form A suitable for steep tapers 40M	308670 40M
ER collet Nominal clamping Ø d 6 mm	308901 6
Torque insert for ER Mini nuts for ER collet chuck 16	309745 16
ER collet for machine taps with seal Nominal clamping Ø d 7 mm	309402 7
ER collet Nominal clamping Ø d 7 mm	308901 7
Wrench for pull studs DIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
ER collet Nominal clamping Ø d 7 mm	308920 7
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 3,5 mm	309445 3,5
Pull stud Hurco 45° with fit sealed suitable for steep tapers 40	308802 40
ER collet Nominal clamping Ø d 8 mm	308901 8
Pull stud Mori-Seiki, sealed, form A suitable for steep tapers 40	308630 40
Special pull stud with no internal thread sealed suitable for steep tapers 40	308700 40
ER collet for machine taps with seal Nominal clamping Ø d 9 mm	309403 9
ER collet for machine taps with seal Nominal clamping Ø d 8 mm	309402 8
ER collet with seal Nominal clamping Ø d 8 mm	308921 8
ER collet Nominal clamping Ø d 1 mm	308920 1
ER collet for machine taps with seal Nominal clamping Ø d 7 mm	309403 7
Pull stud sealed suitable for steep tapers 40	308660 40
ER collet with seal and spray nozzles Nominal clamping Ø d 10 mm	308922 10

ER collet set 10 pieces 1–10 mm	309012
ER collet with seal Nominal clamping Ø d 5 mm	308906 5
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 2,8 mm	309425 2,8
Special pull stud with internal thread suitable for steep tapers 40	308740 40
ER chuck key for ER collet chuck 40	309680 40
ER collet with seal Nominal clamping Ø d 8 mm	308906 8
Pull stud 90° sealed suitable for steep tapers 40	308790 40
ER chuck key for ER collet chuck 16	309680 16
ER collet for machine taps with seal Nominal clamping Ø d 8 mm	309403 8
ER collet with seal and spray nozzles Nominal clamping Ø d 6 mm	308922 6
ER collet Nominal clamping Ø d 4 mm	308901 4
ER collet with seal and spray nozzles Nominal clamping Ø d 5 mm	308922 5
Torque insert for Pull studs to DIN 69872 suitable for ISO taper size 40	308810 40
ER collet Nominal clamping Ø d 10 mm	308920 10
ER collet Nominal clamping Ø d 1 mm	308901 1
ER collet with seal Nominal clamping Ø d 10 mm	308921 10
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 6 mm	309425 6
ER collet with seal and spray nozzles Nominal clamping Ø d 4 mm	308922 4
ER collet Nominal clamping Ø d 1,5 mm	308901 1,5
Pull stud Form B suitable for steep tapers 40	308640 40
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 4 mm	309445 4
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 4,5 mm	309445 4,5
	309445 2,8

ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 2,8 mm	
ER collet for machine taps with seal Nominal clamping Ø d 3,5 mm	309402 3,5
ER collet Nominal clamping Ø d 2 mm	308920 2
ER collet with seal and spray nozzles Nominal clamping Ø d 8 mm	308922 8
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 4,5 mm	309425 4,5
ER collet with seal and spray nozzles Nominal clamping Ø d 3 mm	308922 3
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 2 mm	309445 2
ER collet with seal Nominal clamping Ø d 7 mm	308921 7
ET collet with radial compensation for tapping and reaming Nominal clamping Ø d 6 mm	309445 6
ER collet set 15 pieces 2–16 mm	309240
Pull stud 60° sealed suitable for steep tapers 40	308785 40
ER collet for machine taps with seal Nominal clamping Ø d 6 mm	309402 6
Pull stud 45° sealed suitable for steep tapers 40	308765 40
ER collet set 6 pieces, 3, 4, 5, 6, 8, 10 mm with seal	309014
ET collet for thread tapping, with axial compensation Nominal clamping Ø d 3,5 mm	309425 3,5
Pull stud sealed, form A suitable for steep tapers 40	308610 40
ER collet for machine taps with seal Nominal clamping Ø d 4 mm	309402 4