

**FLUKE.****Clamp meter, Type: 365****Order data**

Order number	473290 365
GTIN	095969559874
Item class	47H

**Description****Version:**

Current clamps with large easy-to-read LCD display in a slim and ergonomic design. Additionally display with backlight. Removable pliers for easier measurement.

**Standard:**

**EN 61010-1**

**Supplied with:**

Incl. test leads and padded carrying case. Batteries 2 pcs. No. 081561 size LR6.

**Technical description**

Memory function	HOLD
Power supply	Battery-powered
Number of batteries contained	2
Article no of the battery / rechargeable battery fitted	081561 LR6
Overvoltage category	CAT III 600 V
AC current	0.1 A – 200 A

Measurement process	TRUE RMS (AC)
Basic accuracy	2 %
Resistance	0.1 $\Omega$ – 6 k $\Omega$
DC current	0.1 A – 200 A
Information displayed	6000
DC voltage	0.1 V – 600 V
maximum jaw aperture	18 mm
AC voltage	0.1 V – 600 V
Power supply	2× 081561 LR6
Standard	EN 61010-1
Calibration	I4
Type of product	Current clamp

## Services

CalibrationClamp meter Type D	027050 D
DAkkS calibrationClamp meter Type D	027060 D

## Accessories

Alkaline-manganese batteries International size LR6	081561 LR6
---	------------