

**LED hand-held stroboscope, Type: 476****Order data**

Order number	471200 476
GTIN	4029547001772
Item class	47B

**Description****Version:**

High adjustment accuracy and stability thanks to dynamic response of the control wheel. High light intensity thanks to energy-efficient electronic circuitry and high-performance Xenon flash lamp. Memory function (last value is saved when switching off the device). Trigger input for synchronising the flash sequence. Stand connection on the casing. Battery life of min. 2 hours.

**Application:**

For measuring very small objects or in inaccessible locations – without interrupting ongoing operations. Ideal for measuring rotational speed and for inspecting parts that move at a high frequency.

**Supplied with:**

Incl. carrying case, charger with 4 country adapters and trigger signal plug.

**Technical description**

Height	50 mm
Power supply	Battery-powered
Operating temperature	0 - 40 °C

Number of batteries contained	6
Error limit	0.01 ( $\pm 1$ digit) %
Article no of the battery / rechargeable battery fitted	081561 LR6
Width	65 mm
Measuring range	30 - 12500 min <sup>-1</sup>
Length	240 mm
Weight	415 g
Calibration	I2
Type of product	Stroboscope

## Services

CalibrationTachometer / stroboscope Type D	027900 D
--	----------

## Accessories

Alkaline-manganese batteries International size LR6	081561 LR6
---	------------