

Fluteless machine tap with oil grooves HSS-E-PM Form E 6HX, TiN, M: M10



Order data

Order number	139185 M10
GTIN	4045197509246
Item class	11H

Description

Version:

DIN 2174 (\approx DIN 371 \leq M10; \approx DIN 376 \geq M12). With oil grooves; optimum lubrication effect even in deeper threads.

Tolerance class: ISO 2X/6HX.

Form E (lead-in: 1.5 - 2 turns) for deep threads with short run-out. The thread is tapped almost to the bottom of the hole.

The innovative polygon form permits a wide application spectrum. The multi-function layer structure achieves maximum service life even in high-tensile materials.

Tolerance class: ISO 2X 6HX

Thread pitch: 1.5 mm Overall length L: 100 mm Shank Ø D_s: 10 mm Shank square □: 8 mm

Tapping hole Ø guide value: 9.35 mm

Technical description

Thread Ø	10 mm
Number of cutting edges Z	5
Number of clamping slots	5
Thread pitch	1.5 mm
Shank Ø D _s	10 mm
Shank square □	8 mm
Overall length L	100 mm

Tapping hole Ø guide value	9.35 mm
Tolerance class	ISO 2X 6HX
Thread depth	30 mm
Thread size	M10
Coating	TiN
Thread type	M
Flank angle	60 degrees
Tool material	HSS E PM
Standard	DIN 2174
Thread standard	DIN 13
Taper lead form	E
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for blind holes and through holes
Cutting direction	right-hand
Colour ring	green
Type of product	Fluteless tap