



LED machine lamp Ring, Type: 160mm



Order data

Order number	081439 160
GTIN	4260131238895
Item class	08C

Description

Version:

Sturdy LED machine lamps in an **aluminium casing**, with a satinised acrylic lens for **homogeneous 160-degree illumination**.

- **Low-reflection, non-dazzle and non-flicker.**
- **For connection to a 24 V mains adapter or 24 V machine control system.**

Ring illumination "circle light" for shadow-free 360° illumination around the spindle on milling machines and drilling machines. Flexible attachment to different types of machine using the adjustable magnetic holder.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

With rubber-clad magnets, mains adapter.

Technical description

Overall height	42 mm
Power supply	Mains operated
Light output	7.5 W
Bulb	LED module
IP Index of Protection	IP 67

Illumination	460 lm
ATEX zone	no
Nominal voltage	24 V
Internal Ø	100 mm
External Ø	160 mm
Type of product	Machine lamp