

**Garant**

**Side lock arbor Form ADB with cooling channel bores, SK 50 A = 200,  
Clamping range  $\varnothing$  D1: 12mm**


**Order data**

|              |               |
|--------------|---------------|
| Order number | 300371 12     |
| GTIN         | 4062406418243 |
| Item class   | 31A           |

**Description**
**Version:**

With Balluff/RFID chip bore.

**GARANT –**

All shanks hard turned (for smooth cutting action!). Balancing quality G 2.5 / G 25,000 rpm

**With coolant supply holes that can be plugged.**

**Application:**

For clamping tools with side flat to DIN 1835 B and DIN 6535 HB.

**Optional extras:**

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

**Technical description**

|                                       |               |
|---------------------------------------|---------------|
| Spare clamping screw No. 30 9900      | 12            |
| External $\varnothing$ D              | 42 mm         |
| Clamping $\varnothing$ D <sub>1</sub> | 12 mm         |
| Overhang dimension A                  | 200 mm        |
| Adapter                               | SK 50 A = 200 |
| Standard                              | DIN 6359      |
| Arbor standard                        | ISO 7388-1    |
| Shape                                 | ADB           |

|                                       |                     |
|---------------------------------------|---------------------|
| Cooling channel bore                  | pluggable           |
| Balance quality G at rotational speed | G 2.5 at 25,000 rpm |
| Concentricity                         | ≤ 3 μm              |
| Machining strategy                    | HPC                 |
| Type of product                       | Side lock arbor     |

## Accessories

|   |           |
|---|-----------|
| Pull studsealed, form A suitable for steep tapers 50                                    | 308610 50 |
| Pull studForm B suitable for steep tapers 50  | 308640 50 |
| Pull stud 45°sealed suitable for steep tapers 50  | 308765 50 |
| Pull stud 90°sealed suitable for steep tapers 50  | 308790 50 |
| Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 50                         | 308615 50 |
| Pull stud 45°sealed suitable for steep tapers 50  | 308760 50 |
| Pull stud 60°sealed suitable for steep tapers 50  | 308785 50 |
| Pull studForm A suitable for steep tapers 50  | 308600 50 |
| Pull studsealed, form B suitable for steep tapers 50                                    | 308620 50 |
| Special pull stud with internal thread suitable for steep tapers 50                     | 308740 50 |
| Pull stud 90°sealed suitable for steep tapers 50  | 308795 50 |
| Pull studsealed, form B suitable for steep tapers 50                                    | 308650 50 |
| Pull stud, 18CrNiMo7Form A suitable for steep tapers 50                                 | 308605 50 |
| Special pull stud with no internal threadsealed suitable for steep tapers 50            | 308720 50 |
| Pull studsealed suitable for steep tapers 50  | 308660 50 |
| Wrench for pull studsISO 7388 suitable for ISO taper size 50                            | 308830 50 |
| Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 50 | 308820 50 |
|   | 309900 12 |

Spare clamping screw for chucks with clamping  $\varnothing$  D1 12 mm

---