


**Garant****GARANT Master Mute cutting head, left-hand, System / insert size: DM/52****Order data**

Order number	264839 DM/52
GTIN	4251414902893
Item class	29D

**Description****Version:**

For threading inserts size 22.

**Suitable for:**

Boring bar shanks No. 264930, 264934 and 264938.

**Note:**

Combination of all cutting heads with all boring bar shanks within the same system (GL, QC, DM) possible.

Through-coolant: yes

System: DM

Cutting point / joint: 40 mm

ISO code cutting head: DIL

suitable indexable insert: 22

Approach angle: 90 °

Minimum pre-drill  $\varnothing D_{\min}$ : 48 mm

Centre offset  $L_3$ : 25 mm

**Technical description**

Approach angle	90 °
Shim screw	259027 2
Shim	279820 4
Cutting point / joint	40 mm
System	DM
Series	Master Mute
ISO code cutting head	DIL
Overall length L	40 mm
suitable indexable insert	22
Clamp, screw, O-ring	279835 4
Centre offset L <sub>3</sub>	25 mm
Minimum pre-drill $\varnothing D_{\min}$	48 mm
Application type	left-hand
Through-coolant	yes
Type of product	Cutting head

## Accessories

Shim Type 4	279820 4
Shim Type 1	279820 1
Clamp unit Type 2	279835 2
Shim screw Type 2	259027 2