

Garant

GARANT Master Steel SPEED solid carbide drill, Weldon shank DIN 6535 HB, TiAlN, Ø DC h7: 6,06-Xmm



Order data

| | |
|--------------|---------------|
| Order number | 123026 6,06-X |
| GTIN | 4062406522957 |
| Item class | 11E |

Description

Version:

Developed for use with **very high cutting speeds**. Outstandingly suitable for machines with **low installed power** and high speeds.

- **Clear reduction in cutting forces due to special cutter geometry.**
- **Coating for best wear resistance even at high process temperatures.**
- **Polished flutes for good chip clearance.**

A **slim chisel point** and the **special arrangement of the 4 guide chamfers** ensure **high positioning and alignment accuracy**. Optimised micro-geometry for increased working life and performance capability.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$. Delivery time: 12 working weeks

Minimum order quantity: 3 pcs

Items made to order for a specific customer: Cancellation only up to a maximum of 3 working days after receipt of order acknowledgement. Items cannot be returned. We reserve the right to over-deliver or under-deliver by $\pm 10\%$ (minimum 1 piece).

Technical description

| | |
|--|-------------------------|
| Flute length L_c | 76 mm |
| Standard | Manufacturer's standard |
| Feed f in steel < 1100 N/mm ² | 0.125 mm/rev. |
| Overall length L | 114 mm |
| Tolerance nominal \varnothing | h7 |

| | |
|---------------------------|-------------------|
| Number of cutting edges Z | 2 |
| Ø range | 6.06 - 8.05 mm |
| Shank Ø D _s | 8 mm |
| Series | Master Steel |
| Coating | TiAlN |
| Tool material | Solid carbide |
| Version | 8×D |
| Point angle | 135 degrees |
| Shank | DIN 6535 HB to h6 |
| Through-coolant | yes, to 25 bar |
| Machining strategy | HPC |
| Semi-Standard | yes |
| Colour ring | green |
| Type of product | Jobber drill |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Steel < 500 N/mm ² | suitable | 195 m/min | P |
| Steel < 750 N/mm ² | suitable | 150 m/min | P |
| Steel < 900 N/mm ² | suitable | 135 m/min | P |
| Steel < 1100 N/mm ² | suitable | 125 m/min | P |
| Steel < 1400 N/mm ² | suitable | 80 m/min | P |
| INOX < 900 N/mm ² | suitable only under restricted conditions | 65 m/min | M |
| GG | suitable | 120 m/min | K |
| GGG | suitable | 115 m/min | K |
| Uni | suitable | | |
| wet maximum | suitable | | |
| wet minimum | suitable | | |

