

Garant

Solid carbide HPC drill Weldon shank DIN 6535 HB, TiAlN, Ø DC h7: 16,06-Xmm



Order data

Order number	123115 16,06-X
GTIN	4062406523220
Item class	11E

Description

Version:

Cutting chisel edge with **high centring accuracy** due to **strong core and special point geometry**.

Particularly high alignment accuracy due to **4 guide chamfers** which stabilise the drill even at extreme depths!

Straight major cutting edges with honed edges and special flute profile for **short chips**, even on long chipping materials.

Advantage:

High process reliability and surface quality of the hole.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$. Delivery time: 12 working weeks

Minimum order quantity: 3 pcs

Items made to order for a specific customer: Cancellation only up to a maximum of 3 working days after receipt of order acknowledgement. Items cannot be returned. We reserve the right to over-deliver or under-deliver by $\pm 10\%$ (minimum 1 piece).

Technical description

Shank tolerance	h6
Number of cutting edges Z	2
Tolerance nominal Ø	h7
Overall length L	262 mm
Flute length L_c	210 mm
Ø range	16.06 - 18.05 mm

Feed f in stainless steel < 900 N/mm ²	0.2 mm/rev.
Standard	Manufacturer's standard
Shank Ø D _s	18 mm
Coating	TiAlN
Tool material	Solid carbide
Version	10xD
Point angle	135 degrees
Shank	DIN 6535 HB to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	blue
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	200 m/min	N
Alu > 10% Si	suitable only under restricted conditions	180 m/min	N
Steel < 500 N/mm ²	suitable	110 m/min	P
Steel < 750 N/mm ²	suitable	80 m/min	P
Steel < 900 N/mm ²	suitable	70 m/min	P
INOX < 900 N/mm ²	suitable	65 m/min	M
INOX > 900 N/mm ²	suitable	55 m/min	M
Ti > 850 N/mm ²	suitable	25 m/min	S
Uni	suitable only under restricted conditions		
wet maximum	suitable		
wet minimum	suitable		

