

## Garant

**Solid carbide HPC drill Weldon shank DIN 6535 HB, TiAlN, Ø DC h7: 3,76-Xmm**



### Order data

Order number	123302 3,76-X
GTIN	4062406523534
Item class	11E

### Description

#### Version:

Cutting chisel edge with **high centring accuracy** due to **strong core and special point geometry**.

Particularly high alignment accuracy due to **4 guide chamfers** which stabilise the drill even at extreme depths!

**Convex cutting edges** with honed edges and special flute profile for **short chips**, even on long chipping materials.

#### Advantage:

**High process reliability and surface quality of the hole.**

#### Note:

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

For process reliability when using the 12xD deep-hole drill, an initial centre drilling with No. 121068 – 121130 or 3xD pilot drilling operation with No. 122736 is necessary.

#### **NEW GENERATION AVAILABLE!**

**Recommended successor products are No. 123226 and 123236.** Delivery time: 12 working weeks

Minimum order quantity: 3 pcs

Items made to order for a specific customer: Cancellation only up to a maximum of 3 working days after receipt of order acknowledgement. Items cannot be returned. We reserve the right to over-deliver or under-deliver by  $\pm 10\%$  (minimum 1 piece).

### Technical description

Standard	Manufacturer's standard
Shank $\varnothing D_s$	6 mm
Feed f in steel < 1100 N/mm <sup>2</sup>	0.1 mm/rev.

Tolerance nominal $\varnothing$	h7
Overall length L	102 mm
$\varnothing$ range	3.76 - 4.75 mm
Number of cutting edges Z	2
Flute length $L_c$	64 mm
Shank tolerance	h6
Coating	TiAlN
Tool material	Solid carbide
Version	12xD
Point angle	135 degrees
Shank	DIN 6535 HB to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Pilot drill required	yes, pilot drill
Semi-Standard	yes
Colour ring	green
Type of product	Jobber drill

## User data

	Suitability	$V_c$	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	180 m/min	N
Alu > 10% Si	suitable only under restricted conditions	140 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable only under restricted conditions	110 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	90 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	80 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	50 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	35 m/min	P

INOX < 900 N/mm <sup>2</sup>	suitable only under restricted conditions	40 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable only under restricted conditions	35 m/min	M
GG(G)	suitable	70 m/min	K
Uni	suitable		
wet maximum	suitable		