




Solid carbide milling cutter HPC, TiSi, Ø f8 DC: 20mm



Order data

Order number	202995 20
GTIN	4045197494108
Item class	12X

Description

Version:

Special TiSi coating.

Note:

NEW GENERATION AVAILABLE!

Recommended successor products are No. 203013, 203015, 203021, 203027.

Technical description

Cutting edge Ø D _c	20 mm
Feed f _z for side milling in INOX > 900 N/mm ²	0.08 mm
Corner chamfer width at 45°	0.3 mm
No. of teeth Z	4
Feed f _z for slot milling in stainless steel > 900 N/mm ²	0.07 mm
Shank Ø D _s	20 mm
Overall length L	92 mm
Flute length L _c	26 mm
Direction of infeed	horizontal, oblique and vertical
Shank	DIN 6535 HB to h6
Tolerance nominal Ø	f8
Helix angle	35 degrees

Corner chamfer angle	45 degrees
Coating	TiSi
Tool material	Solid carbide
Standard	DIN 6527
Type	N
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	0.5×D for side milling
Cutting width a_e for milling operation	Full slot cutting depth 1×D
Through-coolant	no
Machining strategy	HPC
Colour ring	blue
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Steel < 500 N/mm ²	suitable	240 m/min	P
Steel < 750 N/mm ²	suitable	220 m/min	P
Steel < 900 N/mm ²	suitable	180 m/min	P
Steel < 1100 N/mm ²	suitable	180 m/min	P
Steel < 1400 N/mm ²	suitable	150 m/min	P
TOOLOX 33	suitable	115 m/min	H
TOOLOX 44	suitable	80 m/min	H
INOX < 900 N/mm ²	suitable	90 m/min	M
INOX > 900 N/mm ²	suitable	80 m/min	M
Uni	suitable only under restricted conditions		
wet maximum	suitable		

wet minimum	suitable only under restricted conditions
dry	suitable
Air	suitable