

Garant
Solid carbide roughing end mill, short HPC, TiAlN, Ø d11 DC: 9mm


Order data

Order number	205482 9
GTIN	4045197551672
Item class	11X

Description

Version:

With special knuckle profile.

Dimensions similar to DIN 6527.

For high feed rates, very high metal removal rate.

Note:

NEW GENERATION AVAILABLE!

Recommended successor product No. 205548.

Technical description

Feed f_z for slot milling in steel $< 900 \text{ N/mm}^2$	0.04 mm
Corner chamfer width at 45°	0.5 mm
Feed f_z for side milling in steel $< 900 \text{ N/mm}^2$	0.045 mm
No. of teeth Z	4
Cutting edge $\varnothing D_c$	9 mm
Shank $\varnothing D_s$	10 mm
Overall length L	66 mm
Flute length L_c	13 mm
Direction of infeed	horizontal, oblique and vertical
Shank	DIN 6535 HB to h6
Tolerance nominal \varnothing	d11

Helix angle	30 degrees
Corner chamfer angle	45 degrees
Coating	TiAlN
Tool material	Solid carbide
Standard	DIN 6527
Milling profile	HR
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	0.5×D for side milling
Cutting width a_e for milling operation	Full slot cutting depth 1×D
Through-coolant	no
Machining strategy	HPC
Colour ring	green
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	280 m/min	N
Alu > 10% Si	suitable only under restricted conditions	200 m/min	N
Steel < 500 N/mm ²	suitable	120 m/min	P
Steel < 750 N/mm ²	suitable	105 m/min	P
Steel < 900 N/mm ²	suitable	100 m/min	P
Steel < 1100 N/mm ²	suitable	70 m/min	P
Steel < 1400 N/mm ²	suitable	60 m/min	P
Steel < 55 HRC	suitable only under restricted conditions	35 m/min	H
INOX < 900 N/mm ²	suitable	60 m/min	M
INOX > 900 N/mm ²	suitable	50 m/min	M
GG(G)	suitable	90 m/min	K

Uni	suitable
wet maximum	suitable
wet minimum	suitable only under restricted conditions
dry	suitable only under restricted conditions
Air	Suitable only under restricted conditions