

**Mini milling cutter HSS-Co8, uncoated, Ø e8 DC: 2,8mm****Order data**

Order number	191360 2,8
GTIN	4045197102003
Item class	12W

Description**Version:**

Centre cutting teeth for plunging.

Eccentric relief ground. Shank similar to DIN 1835 B with shank tolerance h6. General-purpose cutting edge geometry. For use as **slot drill or end mill** in side lock arbors and collet chucks.

High cutting performance, very competitive price. For milling keyways.

Note:

Save the regrinding costs: it is cheaper to use a mini slot drill to the limit of wear and throw it away, than to regrind it.

Technical description

Feed f_z for slot milling in steel $< 750 \text{ N/mm}^2$	0.003 mm
No. of teeth Z	3
Cutting edge Ø D_c	2.8 mm
Shank Ø D_s	6 mm
Overall length L	36 mm
Flute length L_c	5 mm
Direction of infeed	horizontal, oblique and vertical
Shank	HB with h6
Tolerance nominal Ø	e8
Helix angle	30 degrees

Corner chamfer angle	90 degrees
Coating	uncoated
Tool material	HSS Co 8
Standard	Manufacturer's standard
Type	N
Through-coolant	no
Colour ring	without
Type of product	End / face mill

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	83 m/min	N
Steel < 500 N/mm ²	suitable	30 m/min	P
Steel < 750 N/mm ²	suitable	25 m/min	P
Steel < 900 N/mm ²	suitable	25 m/min	P
CuZn	suitable only under restricted conditions	55 m/min	N
wet maximum	suitable		